
Loose Tube Fibre Optic Outdoor Cable

6 Element All Dielectric Dry Core Design





Issue January 2019 according to Customised OFS Generic Specification



Application

Air-Blown Installation into Micro-Ducts

Design

- Optical Fibres
- Non-metallic Central Member
- Gel-filled Buffer Tubes
- Ripcord
- PE-Jacket

Features

- Small tubes for a reduced outer diameter
- Dry Core Design Cable core water blocked by means of dry "water swellable" technology
 for quicker, cleaner cable prep for jointing
- Individual coloured tubes

Version illustrated is the 72 Fibre Cable

| Article Number | Fibre Count | Tubes | Core Design | Outer Diameter [mm] | Cable Weight [kg/km] | AT-Code** |
|-------------------|--------------|-------|------------------|---------------------------|----------------------------|----------------|
| 12 Singlemode Fib | res per Tube | | | | | |
| K1-3542 | 12 | 1 | 1+6 (5 Fillers*) | 5.2 | 25 | AT-3CE453T-012 |
| K1-3491 | 24 | 2 | 1+6 (4 Fillers*) | 5.2 | 25 | AT-3CE453T-024 |
| K1-3481 | 48 | 4 | 1+6 (2 Fillers*) | 5.2 | 25 | AT-3CE453T-048 |
| K1-3482 | 72 | 6 | 1+6 | 5.2 | 25 | AT-3CE453T-072 |

This table shows nominal diameter and weight values which may differ in shipments.

Identification

Tube and Fibre Colour Code:

| 1 | Blue | 2 | Orange | 3 | Green | 4 | Brown | 5 | Grey | 6 | White |
|---|------|---|--------|---|--------|----|--------|----|------|----|-------|
| 7 | Red | 8 | Black | 9 | Yellow | 10 | Violet | 11 | Rose | 12 | Agua |

Sheath Marking

OFS OPTICAL CABLE MIDIA MICRO GX [ID] [MM/YYYY] [Handset Sign] xxxF [Meter Marking]

^{*} Fillers are natural coloured and evenly distributed over the positions.

^{**} Please refer to the OFS AT- Code.

Loose Tube Fibre Optic Outdoor Cable

6 Element All Dielectric Dry Core Design





Issue January 2019 according to **Customised OFS Generic Specification**

Mechanical Properties and Environmental Behaviour

Tests according to IEC 60794

| Tensile Performance: IEC 60794-1-21-E1A and E1B | Parameter Short term load, during installation | Requirement - No changes in attenuation before versus after load - Max. fibre strain 0.5% | Value Load: 600 N |
|---|--|---|--|
| Crush Performance: IEC 60794-1-21-E3A | Short term load | No changes in attenuation before versus after load No damage** | Load (Plate / Plate): 500 N |
| Bending Performance: | Handling fixed installed | - No attenuation increase* | Bend radius: 90 mm |
| IEC 60794-1-21-E11 | During installation (under Load) | - No changes in attenuation before versus after load | Bend radius: 150 mm |
| Temperatures: IEC 60794-1-22-F1 | Operation Installation Storage/Shipping | - No attenuation increase* | -40 to +70°C -15 to +40°C -40 to +70°C |

^{*}No changes in attenuation means that any changes in measurement value, either positive or negative within the uncertainty of measurement shall be ignored. The total uncertainty of measurement shall be less than of equal to 0.05 dB.

Shipping Information

| Cable Length | Drum Dimensions | (approx.) | Shipping Weight (calc.) | | |
|--------------|--------------------|-----------|-------------------------|--------------|--|
| | Diameter(battened) | Width | Without lagging | With lagging | |
| 2000 m | 1050 mm | 790 mm | 110 kg | 130 kg | |
| 4000 m | 1050 mm | 790 mm | 160 kg | 180 kg | |
| 6000 m | 1050 mm | 790 mm | 210 kg | 230 kg | |
| 8000 m | 1050 mm | 790 mm | 260 kg | 280 kg | |

The shipping information are given for one-way reels. Reusable reels are available on request.

The information is believed to be accurate at time of issue.

OFS reserves the right to improve, enhance and modify the features and specifications of OFS products without prior notification. Please ensure you have the latest version of the data sheet.

This data sheet is property of OFS.

For additional information please contact your sales representative.

You can also visit our website at http://www.ofsoptics.com.

Telephone: +49 (0) 228 7489 201 Email: cableinfo@ofsoptics.com

MiDia® is a registered trademark of Fitel USA Corp.



^{**} Mechanical damage – when examined visually without magnification, there shall be no evidence of damage to the sheath. The imprint of plates will not be considered as damage.